

### Features

- 5" (127 mm) gooseneck spout reach
- Gooseneck spout swivels for unobstructed use of the sink
- Two Lever handles offer separate control of hot and cold water
- Aerated flow
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- Quarter-turn washerless ceramic disc valves
- Less drain

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- For 4" (102 mm) centers
- Three-hole installation

### Recommended Products/Accessories

K-23723 Faucet cleaner



ADA CSA B651

### Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

IAPMO Certification

### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
---	----	-----------------

