



Purist®
15" flush-mount
K-30624-FMLED

Features

- Rounded glass shades connect with gently curved metal bases in contemporary designs fit for any room
- Suitable for damp locations, per UL 1598
- Coordinates with faucets and accessories in the Purist collection
- Includes installation hardware
- Fixture is dimmable with a forward phase-cut/TRIAC/leading edge LED dimmer

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- KOHLER finishes resist corrosion and tarnishing

Installation

- Ceiling-mount



Codes/Standards



UL 1598
CSA C22.2 No. 250.0
CA Title 24 JA8


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CPL	Polished Chrome
	2GL	Brushed Moderne Brass



Required Electrical Service

One circuit required.

Lights: 120 V, 0.2 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum, Glass

Lighting Type: Integrated LED

Number of Shades: 1

Shade Type: Etched Glass

Hanging Type: Non-hanging

CRI ≥ 90

Life Span 50000 Hours

Electrical component rating: LED: 60 Hz, 24 W, 1800 Lumens

Notes

Install this product according to the installation instructions.