

## Features

- Unique slanted oval basin
- No faucet holes; requires wall- or counter-mount faucet
- Unique slotted drain creates a sleek look
- No overflow
- Steam generator creates a warm and gentle mist that hydrates skin, aids in makeup removal, and can help alleviate congestion
- Constant Steam functionality allows generator to produce steam at a consistent rate, which greatly reduces temperature fluctuations
- To ensure safety, system automatically goes into sleep mode after 5 minutes if not reactivated by user
- Auto clean function allows user to set steam passageway to be automatically cleaned between uses
- Water tank refilled automatically
- Operates at 41°F – 113°F (5°C - 45°C); input water temperature 41°F - 100.4°F (5°C - 38°C)
- Adjust steam on/off and volume with included deck-mount digital control
- AC-powered operation—no batteries required (requires 16A power outlet)
- \*Steam can produce mold; ventilate bathroom after use

## Material

- Vitreous china basin
- Generator is constructed of powder-coated mild steel
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Vessel sink
- Generator attaches under counter to bottom of sink

## Included Components

1460429 Drain Lid Assembly






## Codes/Standards

None Applicable

## KOHLER® India Vitreous and bathing Product Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Min. base cabinet width: 36" (914 mm)

Template: Above-counter, 1486829-IN7, required, included

### Notes

Install this product according to the installation instructions.