

Features


- Contemporary design
- Rotating spout with 360° rotation offers superior clearance for filling pots and cleaning
- 7-9/16" (192 mm) spout reach
- Aerated flow
- Single Lever handle allows for on/off activation, volume, and temperature control
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes flexible supply line

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation


- Single-hole installation (escutcheon plate sold separately)
- Deck-mount



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Notes

Install this product according to the installation instructions.