



**Undertone®**  
Under-Mount Kitchen Sink  
**K-3099**

**Features**

- 39" (990 mm) minimum base cabinet width
- Large/small bowls with high/low design
- 9-1/2" depth left bowl and 5-1/2" depth right bowl
- Includes installation hardware

**Material**

- Premium 18-gauge stainless steel

**Installation**

- Undermount

**Recommended Products/Accessories**

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

**Optional Products/Accessories**

- K-11352 Disposal Flange with Stopper

**Included Components**

- 91915 Hardware Kit



**Codes/Standards**

ASME A112.19.3/CSA B45.4

**KOHLER® Stainless Steel Sinks  
Lifetime Limited Warranty**

See website for detailed warranty information.

**DISCONTINUED** This product has been discontinued.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

2-11-2025 17:51 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



## Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Right

Min. base cabinet width: 39" (991 mm)

Bowl area (Left): Length: 19" (483 mm)  
Width: 22" (559 mm)  
Bowl depth: 9-1/2" (241 mm)

Bowl area (Right): Length: 9" (229 mm)  
Width: 15" (381 mm)  
Bowl depth: 5-1/2" (140 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1040323-7, required, included

## Notes

Install this product according to the installation instructions.