

Features

- Versatile, contemporary design
- Single lever handle allows for on/off activation, volume, and temperature control
- Stationary spout
- 8-11/16" (220 mm) spout reach
- 13.4 gpm (50.7 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Parallel collection

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation


- Requires K-97905T mounting-block (sold separately)
- Floor-mount



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 13.4 gal/min (50.7 l/min)

Drain included: No

Spout:

Spout reach: 8-11/16" (221 mm)

Notes

Install this product according to the installation guide.