

Features

- Single lever handle allows for both volume and temperature control
- 6-5/16" (160 mm) spout reach
- 11.6 gpm (43.9 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Nondiverter spout
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Aleo S bathroom faucet and showering collection

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For two-hole installation
- G 1/2 inlet connection

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.1 gal/min (4.2 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: No

Notes

Install this product according to the installation instructions.