

Features

- Two lever handles offer separate control of hot and cold water
- 6-5/16" (160 mm) spout reach
- 13.4 gpm (50.7 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Diverter spout
- Includes Awaken™ multifunction handshower, holder, and 79" (2000 mm) hose
- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- 2.97 gpm (11.2 lpm) maximum handshower flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Aleo S bathroom faucet and showering collection
- Four-hole installation

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- G 1/2 inlet connection

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum flow: 1.2 gal/min (4.5 l/min)

Notes

Install this product according to the installation instructions.