

KOHLER[®] Faucets

Widespread bathroom sink faucet with lever handles,
8.3 lpm
K-31237T-4

Features

- Two lever handles offer separate control of hot and cold water
- 4-5/16" (110 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER[®] ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes cable drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Aleo S bathroom faucet and showering collection

Material

- Premium metal construction for durability and reliability
- KOHLER[®] finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For 8" (203 mm) centers
- Three-hole installation
- Flexible supply lines simplify installation
- Handles are preassembled on valves to simplify installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.

