

### Features

- Single lever handle allows for both volume and temperature control
- 8-1/2" (216 mm) spout reach
- 13.4 gpm (50.7 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Laminar flow
- Diverter spout
- Includes Shift™ Ellipse wand multifunction handshower and 59" (1500 mm) shower hose
- Multifunction handshower offers full coverage and targeted massage spray settings
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.5 gpm (9.5 lpm) handshower maximum flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Aleo S bathroom faucet and showering collection

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Floor-mount
- G 1/2 inlet connection
- Requires floor-mount bath filler mounting base (sold separately)

### Required Products/Accessories

For freestanding installation  
K-97339 Mounting block for select floor-mount bath fillers

### Recommended Products/Accessories



K-23723 Faucet cleaner



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 13.4 gal/min (50.7 l/min)

Drain included: No

#### Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

### Notes

For use with automatic compensating valves rated at 2.5 gal/min (9.5 l/min) or less.

Install this product according to the installation instructions.