Prologue® | K-31465-1

33" top-/undermount double-bowl kitchen sink

Features

- 36" (914 mm) minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Rounded 0.98" (25 mm) corners are easy to clean
- Single faucet hole
- Sink rack available (sold separately)



Sustainability

Available Colors/Finishes

Color tiles intended for reference only.

NA Stainless Steel

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 17:53 - US-CA

Codes/Standards

ASME A112.19.3/CSA B45.4

Technical Information

All product dimensions are nominal.

Number of Deck Holes:	1
Faucet Hole(s) Size:	1-7/16" (37 mm)
Drain Hole Diameter:	3-5/8" (92 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Equal Bowls
Left Basin Length:	14-3/8" (365 mm)
Left Basin Width:	16-1/8" (410 mm)
Left Basin Depth:	9" (229 mm)
Right Basin Length:	14-3/8" (365 mm)
Right Basin Width:	16-1/8" (410 mm)
Right Basin Depth:	9" (229 mm)

Material

- Premium 18-gauge stainless steel
- KOHLER stainless steel sinks resist corrosion and tarnishing

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-23729 Stainless steel cleaner
- K-31472 Stainless steel sink rack, 12-15/16" x 14-11/16"
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket, less tailpiece
- K-11352 Disposal flange with stopper


Warranty

See website for detailed warranty information.

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 17:53 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Top-mount or undermount

Installation Notes

Install this product according to the installation instructions.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 17:53 - US-CA

THE BOLD LOOK OF KOHLER.