



Prologue®

33" top-/undermount single-bowl kitchen sink
K-31466-1

Features

- 36" (914 mm) minimum base cabinet width
- Single bowl
- 9" (229 mm) depth provides generous workspace
- Rounded corners are easy to clean.
- Single faucet hole

Material

- Premium 18-gauge stainless steel
- KOHLER stainless steel sinks resist corrosion and tarnishing

Installation

- Top-mount or undermount

Recommended Products/Accessories

- K-31473 Sink rack
- K-8799 Sink drain and strainer basket
- K-8801 Sink drain and strainer with tailpiece
- K-23729 Stainless steel cleaner
- K-23726 Drain treatment

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper



Codes/Standards

ASME A112.19.3/CSA B45.4
IAPMO Certification

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

7-3-2024 20:00 - US

THE BOLD LOOK
OF **KOHLER**®



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Min. base cabinet width: 36" (914 mm)

Bowl area (Only): Length: 30" (761 mm)
 Width: 16-1/8" (410 mm)
 Bowl depth: 9" (229 mm)
 Water depth: 9" (229 mm)

With overflow: No

Number of deck holes: 1

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-5/8" (92 mm)

Template: Top-mount/Undermount, 1442591-7, required, included

Notes

Install this product according to the installation instructions.