



Undertone®

31" undermount double-bowl kitchen sink
K-3150

Features

- 36" minimum base cabinet width
- Large/medium bowls
- 9-1/2" depth left bowl and 7-1/2" depth right bowl
- Includes installation hardware

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-6390 Sink rack for Undertone® Preserve™ sinks
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper




Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Left):

- Length: 13-3/4" (349 mm)
- Width: 17-7/8" (454 mm)
- Bowl depth: 9-1/2" (241 mm)
- Water depth: 9-1/2" (241 mm)

Bowl area (Right):

- Length: 13-3/4" (349 mm)
- Width: 15-3/8" (391 mm)
- Bowl depth: 7-1/2" (191 mm)
- Water depth: 7-3/8" (186.9 mm)

Notes

Install this product according to the installation instructions.