



**Undertone®**  
31" undermount double-bowl kitchen sink  
**K-3150**

**Features**

- 36" minimum base cabinet width
- Large/medium bowls
- 9-1/2" depth left bowl and 7-1/2" depth right bowl
- Includes installation hardware

**Material**

- Premium 18-gauge stainless steel

**Installation**

- Undermount

**Recommended Products/Accessories**

- K-6390 Sink rack for Undertone® Preserve™ sinks
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

**Optional Products/Accessories**

- K-11352 Disposal Flange with Stopper





**Codes/Standards**


- ASME A112.19.3/CSA B45.4
- IAPMO Certification

**KOHLER® Stainless Steel Sinks  
Lifetime Limited Warranty**

See website for detailed warranty information.



\* Allow clearance around sink rim for clip attachment.



### Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Left):  
 Length: 13-3/4" (349 mm)  
 Width: 17-7/8" (454 mm)  
 Bowl depth: 9-1/2" (241 mm)  
 Water depth: 9-1/2" (241 mm)

Bowl area (Right):  
 Length: 13-3/4" (349 mm)  
 Width: 15-3/8" (391 mm)  
 Bowl depth: 7-1/2" (191 mm)  
 Water depth: 7-3/8" (186.9 mm)

### Notes

Install this product according to the installation instructions.