



Undertone® Trough

22" undermount single-bowl kitchen sink
K-3154

Features

- 27" (686 mm) minimum base cabinet width
- Single bowl
- 4-7/8" (124 mm) depth
- Includes installation hardware, wire storage basket, and wire rack

Material

- Handcrafted from 16-gauge stainless steel
- Premium 16-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-3136 Sink Rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper

Included Components

- K-3127 Wire storage basket for Undertone® trough sinks
- K-3136 Sink Rack
- 91915 Hardware Kit



ADA

Codes/Standards

ASME A112.19.3/CSA B45.4
ADA
ICC/ANSI A117.1
IAPMO Certification

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

10-17-2024 23:24 - US/CA

THE BOLD LOOK
OF **KOHLER**®



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 24" (610 mm)

Bowl area (Only):
 Length: 20" (508 mm)
 Width: 6-1/4" (159 mm)
 Bowl depth: 4-7/8" (124 mm)
 Water depth: 4-7/8" (124 mm)

With overflow: Yes

Drain hole: 3-5/8" (92 mm)

Template: 1022026-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.