

Features

- 1.28 gpf (4.8 lpf)
- Left-hand Polished Chrome trip lever
- Combines with 31588, 31589 bowl to make a complete 31621-DRY, 31641-DRY toilet
- AquaPiston® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush
- Easy-to-flush canister design requires less force to actuate than a 3" (76 mm) flapper, and has 90% less exposed seal material which resists conditions that cause wear, tear, shrinkage and swelling

Installation

- DryLock™ system saves installation time and helps prevent water leakage
- Standard 12" (305 mm) rough-in

Recommended Products/Accessories

- K-31588 Elongated toilet bowl
- K-31589 Round-front toilet bowl
- K-25986-L Left-hand trip lever



Codes/Standards



ASME A112.19.2/CSA B45.1

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit



Cimarron®
Toilet tank, 1.28 gpf
K-31615-DRY

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount
Flush type: AquaPiston, Revolution 360
Rough-in: 12" (305 mm)

Notes

Install this product according to the installation instructions.