

### Features

- Valve Only. Requires KOHLER® glass or metal sensor trim plate and AC or DC power supply (each sold separately) to complete full system solution. Faceplate determines flush volume.
- Designed to be serviceable through faceplate opening
- Adjustable connections for easy installation and servicing
- Fully mechanical manual override
- Lever-handle stop valve for quick and easy water control
- Chloramine and chlorine resistance on all rubber components exposed to waterway
- 125-micron filter protects internal components
- Not for use with PEX piping due to risk of dezincification

### Material

- Durable brass construction

### Installation

- Intended for toilet installations with 1-1/2" (38 mm) rear spud coupling connection




### Codes/Standards

ASSE 1037/ASME A112.1037/CSA B125.37

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

### Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)

Fixture pressure min (static): 35 psi (241.3 kPa)

Min flow rate: 25 gpm (94.6 lpm)

### Notes

Install this product according to the installation instructions.