



# Undertone®

41-3/4" undermount triple-bowl kitchen sink  
K-3166

## Features

- 45" (1143 mm) minimum base cabinet width
- 9-1/2" depth left bowl, 5-1/2" depth center bowl, and 7-1/2" depth right bowl
- Rounded bowls
- Sink drain with strainer sold separately

## Material

- Premium 18-gauge stainless steel

## Installation

- Undermount

## Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

## Optional Products/Accessories

- K-11352 Disposal Flange with Stopper

## Included Components

- 91915 Hardware Kit




## Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

## KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Basin configuration: Third Bowl

Min. base cabinet width: 45" (1143 mm)

Bowl area (Left): Length: 14" (356 mm)  
 Width: 18" (457 mm)  
 Bowl depth: 9-1/2" (241 mm)

Bowl area (Center): Length: 9" (229 mm)  
 Width: 15" (381 mm)  
 Bowl depth: 5-1/2" (140 mm)

Bowl area (Right): Length: 14" (356 mm)  
 Width: 18" (457 mm)  
 Bowl depth: 7-1/2" (191 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1047579-7, required, included

## Notes

Install this product according to the installation instructions.