



Two-light sconce K-31762-SC02

### **Features**

- Globular glass shades extend from rods with flared metal detail in elegant transitional designs suited for any room
- Coordinates with other products in the Bellera collection
- Requires two bulbs with candelabra (E12) base; T10 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware

### Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes



### Codes/Standards

UL 1598 CSA C22.2 No. 250.0

# **KOHLER® Indoor Lighting Fixtures Limited Warranty**

See website for detailed warranty information.


### Available Colors/Finishes


Color tiles intended for reference only.

Color	Code	Description
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass









# **Required Electrical Service**

One circuit required.

120 V, 1 A, 60 Hz

## **Technical Information**

All product dimensions are nominal.

Material: Steel, Aluminum, Zinc, Glass

Number of Lights: 2

Lighting Type: Socket-based
Socket Type: E-12 Candelabra

Number of Shades: 2

Shade Type: Glass - clear Hanging Type: Non-hanging

