



**Undertone®**

31-1/2" undermount double-bowl kitchen sink  
**K-3177**

### Features

- 36" minimum base cabinet width
- Large/medium bowls
- 9-1/2" depth left bowl and 7-1/2" depth right bowl
- Includes installation hardware

### Material

- Premium 18-gauge stainless steel

### Installation

- Undermount

### Recommended Products/Accessories

- K-6388 Sink Rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

### Optional Products/Accessories

- K-3294 Hardwood cutting board for kitchen sinks
- K-11352 Disposal Flange with Stopper

### Included Components

- 91915 Hardware Kit



### Codes/Standards

ASME A112.19.3/CSA B45.4  
IAPMO Certification

### **KOHLER® Stainless Steel Sinks Lifetime Limited Warranty**

See website for detailed warranty information.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

12-24-2024 21:02 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



## Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14" (356 mm)  
 Width: 19" (483 mm)  
 Bowl depth: 9-1/2" (241 mm)

Bowl area (Right): Length: 14" (356 mm)  
 Width: 16" (406 mm)  
 Bowl depth: 7-1/2" (191 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1040557-7, required, included

## Notes

Install this product according to the installation instructions.