

Features

- Contoured metal shade uniquely surrounds a single bulb
- Contemporary design will make a statement in any room
- Requires bulbs with medium (E26) base; type G25 frosted bulbs recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Ceiling-mount



Codes/Standards

UL 1598
CSA C22.2 No. 250.0


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	BML	Black, Brass Trim
	SLG	
	6GL	



Required Electrical Service

One circuit required.

120 V, 1.5 A, 60 Hz

Notes

Install this product according to the installation instructions.

Technical Information

All product dimensions are nominal.

Material: Aluminum, Steel
Number of Lights: 3
Lighting Type: Socket-based
Socket Type: E-26 Medium
Number of Shades: 3
Shade Type: Metal
Hanging Type: Non-hanging