



Undertone®

22" undermount single-bowl kitchen sink
K-3179

Features

- Single basin
- Sink can operate as a secondary or prep sink for ultimate flexibility when designing a custom workspace
- If you would like sink K-3179-NA with wire rack and storage basket, please order K-3154-NA

Material

- Premium 18-gauge stainless steel

Recommended Products/Accessories


- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper

Included Components

- 91915 Hardware Kit




Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 24" (610 mm)

Bowl area (Only): Length: 20" (508 mm)
 Width: 6-1/4" (159 mm)
 Bowl depth: 4-7/8" (124 mm)
 Water depth: 4-7/8" (124 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1022026-7, required, included

Notes

Install this product according to the installation instructions.