



Undertone®
under-mount bar sink
K-3182

Features

- 21-inch minimum base cabinet width.
- Single bowl.
- 7-5/8-inch depth.
- No faucet holes.
- SilentShield® sound-absorption technology offers quieter performance.
- Includes installation hardware.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.

Recommended Products/Accessories

K-3132 Sink Rack
K-8801 Sink Strainer
K-8799 Sink Strainer
K-23726 Drain treatment
K-23729 Stainless steel cleaner

Optional Products/Accessories

K-8813 Manual Sink Strainer with Tailpiece
K-8814 Sink Strainer
K-11352 Disposal Flange with Stopper

Included Components

Product consists of:
91915 Hardware Kit



ADA


Codes/Standards

ASME A112.19.3/CSA B45.4
ADA
ICC/ANSI A117.1

Lifetime Limited Warranty for

KOHLER® Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Under-mount

Min. base cabinet width: 21" (533 mm)

Bowl area (Only): Length: 14-1/4" (362 mm)
Width: 18-1/2" (470 mm)
Bowl depth: 7-5/8" (194 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1315836-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.

ADA permits a parallel approach to wet bars.