



# Brockway™

36" wall-mount utility sink  
K-3200-PPB

## Features

- Single bowl
- 36" (914 mm) total width
- Painted Peachblow underside finish
- Requires two K-730T70 faucets one K-8880 soap dish (sold separately)

## Material

- KOHLER® enameled cast iron
- Acid-resistant enamel finish

## Installation

- Wall-mount

## Recommended Products/Accessories

- K-8880 Soap Dish
- K-8820 Sink Drain and Strainer
- K-730T70-4AJR Wall-mount lavatory faucet, 1.2 gpm
- K-730T70-4AR Wall-mount service sink faucet, 12 gpm
- K-23726 Drain treatment
- K-23725 Cast iron cleaner



## Codes/Standards

ASME A112.19.1/CSA B45.2  
IAPMO Certification

## KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty


See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



### Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl  
Min. base cabinet width: 33" (838 mm)

Bowl area (Only): Length: 32" (813 mm)  
Width: 14" (356 mm)  
Water depth: 7" (178 mm)

Number of deck holes: 4

Faucet hole(s): 1-1/2" (38 mm)  
Soap/Lotion hole: 5/16" (8 mm)  
Drain hole: 2-1/8" (54 mm)

### Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the current product template available at [www.kohler.com](http://www.kohler.com) or by calling 1-800-4KOHLER. Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.