

### Features

- Kohler plumbing products mean beautiful form as much as reliable function
- Drilled for two K-730T70 Triton® Bowe® Cannock™ faucets and one K-8880 soap dish
- Sink exterior is an unpainted, ground-coat surface. Submitted pictures are customer photos that may reflect an alteration to the exterior, such as painting or refinishing, and may no longer reflect the raw elements of the cast iron material as purchased

### Material

- KOHLER® enameled cast iron
- Acid-resistant enamel finish

### Recommended Products/Accessories

K-8880 Soap Dish  
K-8820 Sink Drain and Strainer  
K-730T70-4AJR Wall-mount lavatory faucet, 1.2 gpm  
K-730T70-4AR Wall-mount service sink faucet, 12 gpm  
K-23726 Drain treatment  
K-23725 Cast iron cleaner



### Codes/Standards

ASME A112.19.1/CSA B45.2  
IAPMO Certification

### KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes


*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



**Brockway™**  
36" wall-mount utility sink  
**K-3200**



**Technical Information**

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 33" (838 mm)

Bowl area (Only): Length: 32" (813 mm)  
Width: 14" (356 mm)  
Water depth: 7" (178 mm)

Number of deck holes: 4

Faucet hole(s): 1-1/2" (38 mm)

Soap/Lotion hole: 5/16" (8 mm)

Drain hole: 2-1/8" (54 mm)

**Notes**

Install this product according to the installation instructions.