



Vault™
15" top-/undermount single-bowl bar sink
K-32027-1

Features

- 18" (457 mm) minimum base cabinet width
- Single bowl
- 5-1/2" (140 mm) depth
- Single faucet hole
- Optional K-2993 bottom sink rack (sold separately)
- Includes installation hardware

Material

- Premium 18-gauge stainless steel
- KOHLER stainless steel sinks resist corrosion and tarnishing

Installation

- Top-mount or undermount
- Center drain

Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket

Optional Products/Accessories

- K-2993 Sink Rack





ADA

Codes/Standards

- ASME A112.19.3/CSA B45.4
- ADA
- ICC/ANSI A117.1
- IAPMO Certification

**KOHLER® Stainless Steel Sinks
Lifetime Limited Warranty**

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 18" (457 mm)

Bowl area (Only):
 Length: 12-1/4" (311 mm)
 Width: 9-9/16" (243 mm)
 Bowl depth: 5-5/16" (135 mm)
 Water depth: 5-5/16" (135 mm)

Number of deck holes: 1

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-3/4" (94 mm)

Template: Top-mount/Undermount, 1161548-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.