

Features

- Kohler plumbing products mean beautiful form as much as reliable function
- Drilled for two K-730T70 Triton® Bowe® Cannock™ faucets and one K-8880 soap dish
- Sink exterior is an unpainted, ground-coat surface. Submitted pictures are customer photos that may reflect an alteration to the exterior, such as painting or refinishing, and may no longer reflect the raw elements of the cast iron material as purchased

Material

- KOHLER® enameled cast iron
- Acid-resistant enamel finish

Recommended Products/Accessories

K-8820 Sink Drain and Strainer
K-8880 Soap Dish
K-730T70-4AJR Wall-mount lavatory faucet, 1.2 gpm
K-730T70-4AR Wall-mount service sink faucet, 12 gpm
K-23726 Drain treatment
K-23725 Cast iron cleaner



Codes/Standards

ASME A112.19.1/CSA B45.2
IAPMO Certification

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Center(s): 8" (203 mm)

Min. base cabinet width: 21" (533 mm)

Bowl area (Basin #1): Length: 44" (1118 mm)
Width: 14" (356 mm)
Water depth: 7" (178 mm)

Number of deck holes: 4

Faucet hole(s): 1-1/2" (38 mm)

Soap/Lotion hole: 5/16" (8 mm)

Drain hole: 2-1/8" (54 mm)

Notes

Install this product according to the installation instructions.