



## Kernen™ by Studio McGee

18" pendant  
K-32261-PE01

### Features

- Designed in collaboration with Studio McGee
- Flared milk glass shade perfectly diffuses the light to add an elegant warmth to your room
- Requires bulb with medium (E26) base; type A19, A21, or G25 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Coordinates with other products in the Kernen collection
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

### Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes



### Codes/Standards

UL 1598  
CSA C22.2 No. 250.0

### KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SNL	Polished Nickel
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

10-21-2024 01:19 - US/CA

THE BOLD LOOK  
OF **KOHLER**®



### Required Electrical Service

One circuit required.

120 V, 0.833 A, 60 Hz

### Technical Information

All product dimensions are nominal.

Material:	Steel, Glass, Brass, Aluminum
Number of Lights:	1
Lighting Type:	Socket-based
Socket Type:	E-26 Medium
Number of Shades:	1
Shade Type:	Frosted Glass
Hanging Type:	Downrod
Downrod Detail:	2 x 18" (457 mm), 1 x 12" (305 mm), 1 x 6" (152 mm), 1 x 3" (76 mm)
Height:	18-13/16" (478 mm) - 72-13/16" (1850 mm)

### Notes

Install this product according to the installation instructions.