

## Features

- The double-domed metal shade features a cage detail at the connection
- A great piece for any farmhouse- or industrial-style space — especially over a double-vanity sink, or in a guest bathroom, or powder room
- Medium base (E26) socket, works best with type A or G light bulbs (sold separately)
- Suitable for damp locations, per UL 1598

## Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes




## Codes/Standards

UL 1598  
CSA C22.2 No. 250.0

## KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



## Required Electrical Service

One circuit required.

Lights: 120 V, 2.5 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Steel, Aluminum

Number of Lights: 3

Lighting Type: Socket-based

Socket Type: E-26 Medium

Number of Shades: 3

Shade Type: Metal

Hanging Type: Non-hanging

Electrical component rating: Socket Rating: 60 Hz, 100 W