



Glam | K-32510-SC02

Two-light sconce

Features

- Artisan-crafted organic ceramic shades create a soft ambient glow in Hollywood-inspired fixtures
- Requires two bulbs with candelabra (E12) base; G16.5 bulb recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs



Codes/Standards

CSA C22.2 No. 250.0

Technical Information

All product dimensions are nominal.

Number of Lights:	2
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	1
Hanging Type:	Non-hanging

Material

- Ceramic and premium metal construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One circuit required.


120 V, 1 A, 60 Hz

Warranty

See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty





Installation Notes

Install this product according to the installation instructions.

