

Features


- Performance showering packages offer increased functionality and simplify the ordering process
- Includes bath faucet, two shower hoses, shower column, handshower, and rainhead
- Single lever handle allows for on/off activation, volume, and temperature control
- 6-1/4" (159 mm) diverter spout with G 1/2 connection
- 59" (1500 mm) hose connects to shower column base to handshower
- 19-11/16" (500 mm) hose connects trim diverter to shower column base
- Single-function handshower delivers a full, consistent spray, regardless of water pressure
- Sprayface resists hard water buildup and is easy to clean
- Easy-to-adjust handshower holder slides up/down shower column with left-side release; locks in place at your preferred height
- 8" (203 mm) round rainhead
- Diverter at base of column makes for easy toggling between handshower and showerhead
- 2.5 gpm (9.5 lpm) maximum flow rate at 73 psi (5.0 bar)
- Rainhead utilizes Katalyst™ air induction technology, fusing water with air to create bigger drops for a more powerful spray

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing


Installation

- Wall-mount
- G 1/2 inlet connection

**Codes/Standards**

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation guide.