

Features

- Single lever handle allows for both on/off activation and temperature setting
- 4-1/4" (108 mm) spout reach
- 4.0 gpm (15.1 lpm) at 45 psi (3.1 bar)
- Red/blue indexing on handle
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Part of the Accliv bathroom faucet and showering collection
- Drain sold separately

Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner




Codes/Standards

None Applicable

KOHLER India Faucet Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 4.6 gal/min (17.4 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: Yes

Drain with overflow: No

Spout:

Spout reach: 4" (102 mm)

Notes

Install this product according to the installation instructions.