

Features

- Single lever handle allows for both on/off activation and temperature setting
- 9-7/8" (250 mm) spout height
- 5-7/8" (149 mm) spout reach
- 1.85 gpm (7.0 lpm) maximum flow rate at 60 psi (4.14 bar)
- Red/blue indexing on handle
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Accliv bathroom faucet and showering collection

Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories


K-23726 Drain treatment
K-23723 Faucet cleaner

**Codes/Standards**

None Applicable

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.85 gal/min (7 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: Yes

Drain with overflow: Yes

Notes

Install this product according to the installation instructions.