

KOHLER® Faucets Tower paddle-handle bathroom sink faucet, 8.3 lpm

Accliv™
K-33064T-4

Features

- Single lever handle allows for both on/off activation and temperature setting
- 12-3/16" (309 mm) faucet height
- 5-7/8" (149 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Red/blue indexing on handle
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Accliv bathroom faucet and showering collection

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner



Codes/Standards


Plumbing Standards
GB 18145

See website for detailed warranty information.

KOHLER Faucets Tower paddle-handle bathroom sink faucet, 8.3 lpm

Accliv™

K-33064T-4



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 5-13/16" (147 mm)

Notes

Install this product according to the installation instructions.