

# KOHLER® Faucets

Widespread bathroom sink faucet, paddle handles

**Accliv™**  
**K-33065T-4**

## Features

- Two lever handles offer separate control of hot and cold water
- 4-5/16" (110 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes cable pop-up drain with 1-1/4" (32 mm) tailpiece
- Part of the Accliv bathroom faucet and showering collection

## Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- For 8" (203 mm) centers
- Flexible supply lines simplify installation

## Recommended Products/Accessories


K-23726 Drain treatment  
K-23723 Faucet cleaner



## Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach: 4-5/16" (110 mm)

Handle clearance: 8" (203 mm)