

### Features

- Single lever handle allows for both volume and temperature control
- Two spray functions; textured spout switch slides up/down to direct water to bottom/top of spout
- Top-of-spout laminar stream delivers a gentle rinse with minimal splash during your oral hygiene routine
- Sprayhead pulls out on 15" (381 mm) flexible hose for convenient hair washing and sink cleaning
- 8-5/8" (219 mm) faucet height
- 6-3/8" (162 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Red/blue indexing on handle
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Accliv bathroom faucet and showering collection



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.

### Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

### Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach:  $6\text{-}3/8\text{''}$  (162 mm)

### Notes

Install this product according to the installation instructions.