

## Features

- Single lever handle allows for both volume and temperature control
- 5-5/8" (143 mm) spout reach
- 8.0 gpm (30.3 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Diverter spout
- Includes Awaken™ multifunction handshower, holder, and 60" (1524 mm) hose
- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- 2.2 gpm (8.3 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Accliv bathroom faucet and showering collection



## Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.

## Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Deck- or bath-mount
- For two-hole installation
- G 1/2 inlet connection

## Recommended Products/Accessories

K-23723 Faucet cleaner



## Technical Information

All product dimensions are nominal.

Drain included: No

### Spout:

Spout reach: 5-5/8" (143 mm)

### Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

Pressure: 45 psi (3.1 bar)

## Notes

Install this product according to the installation instructions.