

## Features

- Single lever handle allows for both volume and temperature control
- 9-3/8" (238 mm) spout reach
- 8.0 gpm (30.3 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Diverter spout
- Includes Awaken™ multifunction handshower, holder, and 60" (1524 mm) hose
- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- Thumb tab allows for a smooth transition between sprays
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.2 gpm (8.3 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Accliv bathroom faucet and showering collection

## Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Floor-mount
- G 1/2 inlet connection
- Requires floor-mount bath filler mounting base (sold separately)

## Required Products/Accessories

For freestanding installation  
K-97339 Mounting block for select floor-mount bath fillers

## Recommended Products/Accessories

K-23723 Faucet cleaner



## Codes/Standards

Plumbing Standards  
GB 18145


See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

### Color Code Description

	BL	Matte Black
---	----	-------------



## Technical Information

All product dimensions are nominal.

Drain included: No

### Spout:

Spout reach: 8-7/8" (225 mm)

### Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

## Notes

Install this product according to the installation instructions.