

### Features

- Project pack: Supplied three per case
- Modern, simplistic exposed thermostatic valve serves as a hub for shower controls
- Thermostatic valve allows user to set and maintain precise temperature
- Antiscald protection
- Volume control valve provides on/off operation, along with precise control of water volume and intensity
- Includes Citrus multifunction handshower, holder, and 60" (1524 mm) smooth hose
- Multifunction handshower provides four spray experiences: full coverage, concentrated, targeted, and combination spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Accliv bathroom faucet and showering collection



### Codes/Standards

Plumbing Standards  
QB/T 2806

See website for detailed warranty information.

### Material



- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Technology

- Thermostatic technology automatically maintains temperature within +/- 0.4°C (+/- 0.72°F) during water pressure fluctuations

### Installation

- Wall-mount
- G 1/2 inlet connection



### Technical Information

All product dimensions are nominal.

Drain included: No

### Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

Pressure: 45 psi (3.1 bar)

### Notes

Install this product according to the installation instructions.