

Features

- Project pack: Supplied three per case
- Modern, simplistic exposed thermostatic valve serves as a hub for bath/shower controls
- Thermostatic valve allows user to set and maintain precise temperature
- Antiscald protection
- Volume control valve provides on/off operation, along with precise control of water volume and intensity
- Diverter spout
- After shower, diverter automatically returns to default bath faucet position, for a safer next shower experience
- Includes Citrus multifunction handshower, holder, and 60" (1524 mm) smooth hose
- Multifunction handshower provides four spray experiences: full coverage, concentrated, targeted, and combination spray
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Accliv bathroom faucet and showering collection

**Codes/Standards**

Plumbing Standards
QB/T 2806

See website for detailed warranty information.

Material



- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Technology

- Thermostatic technology automatically maintains temperature within $\pm 0.4^{\circ}\text{C}$ ($\pm 0.72^{\circ}\text{F}$) during water pressure fluctuations

Installation

- Wall-mount
- G 1/2 inlet connection



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

Pressure: 45 psi (3.1 bar)

Notes

Install this product according to the installation instructions.