

## Features

- Features integrated 35 mm mixing valve
- Single lever handle allows for both volume and temperature control
- Includes Citrus single-function handshower, holder, and 60" (1524 mm) hose
- Full coverage produces an encompassing spray ideal for everyday use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Part of the Accliv bathroom faucet and showering collection



## Codes/Standards

Plumbing Standards  
GB 18145



## Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

See website for detailed warranty information.

## Installation

- Wall-mount
- G 1/2 inlet connection



### Technical Information

All product dimensions are nominal.

Drain included: No

### Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

### Notes

Install this product according to the installation instructions.