

## Features

- 22-1/4" (565 mm) minimum base cabinet width
- Square basin with a contemporary design
- Single bowl
- Rounded corners are easy to clean
- 7-7/8" (200 mm) depth provides generous workspace
- No faucet hole drilling
- Rear drain increases workspace in the sink and allows for more storage space underneath the sink
- With overflow
- To conceal overflow, pair with optional cover (sold separately)
- Sink strainer sold separately

## Material


- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

## Installation

- Undermount

## Recommended Products/Accessories



K-77810T



## Codes/Standards

None Applicable

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 22-1/4" (565 mm)

Bowl area (Basin #1):  
Length: 16-9/16" (420 mm)  
Width: 16-9/16" (420 mm)  
Bowl depth: 7-5/8" (194 mm)  
Water depth: 6-7/16" (164 mm)

With overflow: Yes

Template: Top-mount/Undermount, 1561311-K7, not required, included

## Notes

Install this product according to the installation instructions.