

Features


- Performance showering packages offer increased functionality and simplify the ordering process
- Coordinates with other products in the Hone™ collection to complete your bathroom
- 2.5 gpm (9.5 lpm) maximum flow rate
- Includes bath faucet trim, shower column, Rain Duet™ handshower, square rainhead, and two shower hoses
- Single lever handle allows for both volume and temperature control
- 6-15/32" (164 mm) spout reach
- Trim includes push button diverter
- 19-11/16" (500 mm) hose connects trim diverter to shower column base
- Modern, simplistic exposed thermostatic column serves as a hub for shower controls
- For use in bath and shower installations with beam shower arm for reduced ceiling height
- Diverter at base of column makes for easy toggling between handshower and showerhead
- 59" (1500 mm) hose connects to shower column base to handshower
- Easy-to-adjust handshower holder slides up/down shower column with left-side release; locks in place at your preferred height
- Multifunction handshower with advanced spray engine provides five spray experiences: full rain, power massage, gentle spray, rain massage, and rain spray
- Thumb tab allows for a smooth transition between sprays
- Unique square 8" (200 mm) single-function rainhead creates a modern look
- Rainhead utilizes Katalyst™ air induction technology, fusing water with air to create bigger drops for a more powerful spray

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall-mount
- G 1/2 inlet connection





Codes/Standards

Plumbing Standards
TIS 2066-2552

See website for detailed warranty information.

KOHLER Faucets Hone™

Three-way shower column, hose connection, 9.5 lpm
K-33224K-4



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.