


Features

- Two-piece design
- Elongated bowl offers added room and comfort
- Rim-to-floor height: 16.26 inch (413 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.5 lpf)
- Washdown flushing system
- 1-15/16" (49 mm) fully glazed trapway
- Skirted trapway simplifies cleaning
- The Complete Solution toilets provide everything you need, including bowl, tank, seat, wax ring, supply line, and hardware
- Closed-front seat with lid
- Quiet-Close™ functionality to prevent seat from slamming
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Specialty hinge component keeps lid open at 90°
- Overhanging lid conceals the seat ring for a clean look

Installation


- Three-bolt quick-connect installation
- Standard 12 inch (305 mm) rough-in



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Washdown
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	8-15/16" (227 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.