



# Undertone® Preserve®

23" undermount single-bowl kitchen sink  
K-3325-HCF

## Features

- 27" (686 mm) minimum base cabinet width
- Single bowl
- 9-1/2" (241 mm) depth provides generous workspace
- Innovative Preserve™ sink resists scratching and withstands everyday wear and tear
- Rear drain placement increases cabinet storage space underneath sink
- Includes bottom sink rack
- Includes installation hardware

## Material

- Premium 18-gauge stainless steel

## Installation

- Undermount

## Recommended Products/Accessories

- K-3192 Sink rack for Iron/Tones® kitchen sinks
- K-6391 Sink rack for Undertone® sinks
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

## Optional Products/Accessories

- K-11352 Disposal Flange with Stopper

## Included Components

- K-6391 Sink rack for Undertone® sinks




## Codes/Standards

ASME A112.19.3/CSA B45.4  
IAPMO Certification

## KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 27" (686 mm)

Bowl area (Center): Length: 21-1/4" (540 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 9-1/2" (241 mm)  
Water depth: 9-1/2" (241 mm)

Drain hole: 3-3/4" (94 mm)

Template: 113193, required, included

### Notes

Install this product according to the installation instructions.