

Features

- Single-function rainhead
- Ultra-slim design
- Optimized sprayface for maximum performance
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Flexible, silicone nozzles assure long life and easy clean
- Adjustable swivel ball joint allows for precise spray adjustment
- 2.5 gpm (9.5 lpm) maximum flow rate at 80 psi (5.5 bar)
- G 1/2 connection

Material


- Durable material construction
- KOHLER finishes resist corrosion and tarnishing

Technology

- With WaterMind™ technology, spray nozzles automatically adjust to changes in water pressure for a consistent shower under varying intensities


Installation

- Installs as a ceiling or wall mount application
- Requires single-function rainhead shower arm and flange (sold separately)

**Codes/Standards**

None Applicable

See website for detailed warranty information.

**Technical Information**

All product dimensions are nominal.

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.