



Undertone® Lyric®
18-1/2" top-/undermount single-bowl bar sink
K-3341

Features

- 24" (610 mm) minimum base cabinet width
- Single bowl
- 7-1/2" (191 mm) depth
- Includes installation hardware

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-8813 Stainless steel sink drain and strainer with tailpiece
- K-11352 Disposal Flange with Stopper

Included Components

- 52047 Clamp Accessory Pack, 4 Ea.




ADA

Codes/Standards

- ASME A112.19.3/CSA B45.4
- ADA
- ICC/ANSI A117.1
- IAPMO Certification

**KOHLER® Stainless Steel Sinks
Lifetime Limited Warranty**

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 24" (610 mm)

Bowl area (Only): Bowl depth: 7-1/2" (191 mm)

Drain hole: 3-5/8" (92 mm)

Template: 113392-7, required, included

Notes

Install this product according to the installation instructions.

Supplied bowl clamp assemblies require 1" (25 mm) minimum countertop thickness. Installer must supply hardware for thinner countertops.

For multiple bowl under-mount installations, a minimum distance of 3-1/2" (89 mm) is required between bowls.

Countertop supplier to determine required support.

Waterproof unprotected overhang area of the underside of wood counter.

ADA compliant when installed to the specific requirements of these regulations.

ADA permits a parallel approach to wet bars.