



**Toccata™**  
Top-mount Kitchen Sink  
**K-3347L-3**

**Features**

- 36-inch minimum base cabinet width.
- Large/small bowls with high/low design.
- 4-1/8-inch left depth and 7-inch right depth.
- Three faucet holes on left side.
- Offset drain increases workspace in the sink and storage space underneath.
- SilentShield® sound-absorption technology offers quieter performance.
- Includes installation hardware.

**Installation**

- Top-mount.

**Recommended Products/Accessories**

K-8801 Sink Strainer  
K-8799 Sink Strainer  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

**Optional Products/Accessories**

K-6139 Sponge Caddy  
1177161 Installation Clip Kit  
K-11352 Disposal Flange with Stopper

**Included Components**

Product consists of:

1177160 Hardware Kit, Self-Rimming




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

|                          |                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------|
| Bowl configuration:      | High-low                                                                          |
| Installation:            | Top-mount                                                                         |
| Cutout:                  | Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1/2" (13 mm) radius corners   |
| Min. base cabinet width: | 36" (914 mm)                                                                      |
| Bowl area (Right):       | Length: 21" (533 mm)<br>Width: 15-1/4" (387 mm)<br>Bowl depth: 7" (178 mm)        |
| Bowl area (Left):        | Length: 7-1/4" (184 mm)<br>Width: 15-1/4" (387 mm)<br>Bowl depth: 4-1/8" (105 mm) |
| Number of deck holes:    | 3                                                                                 |
| Faucet hole(s):          | 1-7/16" (37 mm)                                                                   |
| Drain hole:              | 3-5/8" (92 mm)                                                                    |

## Notes

Install this product according to the installation instructions.