



Anthem™ EvoCycle™ | K-33481

Smart shower system

Features

- Select Standard mode from handshower or Cycle mode from showerhead
- Cycle mode recirculates water for up to 80% in water savings
- Built-in vacuum breaker prevents backflow
- Digital control features touch screen with easy-to-read icons and large temperature control dial
- Ozone cleaning cycle can be run after every use, ensuring shower is ready for next user
- Anthem™ two-port thermostatic digital valve allows for both a handshower and showerhead
- Use with KOHLER Konnect® app for remote start/stop, water-saving tracking, and system updates
- 1/2" (13 mm) valve inlets and outlets with brass tube connections
- Convenient shelf holds shower essentials
- Box includes: Thermostatic digital shower valve, digital control, ozone controller, shower rail, vacuum breaker with shelf, shower receptor cover, electronic components
- Pair with optional Anthem remote on/off button (sold separately)
- Requires KOHLER® Anthem™ EvoCycle™ shower base, showerhead, handshower, and shower hose (each sold separately)
- Cycle mode can reach a max temperature up to 109°F, dependent on bathroom conditions



Available Colors/Finishes

Color tiles intended for reference only.

- CP Polished Chrome
- BN Vibrant Brushed Nickel
- BL Matte Black
- 2MB Vibrant Brushed Moderne Brass



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
5-14-2026 17:0 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.18.1/CSA B125.1
ASME A112.18.2/CSA B125.2
CSA B64
ASSE 1001
ASSE 1016/ASME A112.1016/CSA B125.16

Valves

Included Valve: Digital

Shower Valve

Flow Rate Maximum @ 45 psi: 12 gpm (45.4 l/min)

Manufacturer's Minimum
Rated Flow: 0.9 gpm (3.4 l/min)

Pressure: 45 psi (3.1 bar)

Maximum Static Pressure: 125 psi (8.6 bar)

Minimum Operating Pressure: 20 psi (1.4 bar)

Material

- Brass
 - Thermoplastic resin
 - Thermoplastic-encased valve and ozone controller
 - Durable metal construction
 - KOHLER finishes resist corrosion and tarnishing
-

Connectivity



The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license.


Warranty

See website for detailed warranty information.

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited
Warranty|KOHLER® Faucet Lifetime Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
5-14-2026 17:0 - US-CA



Installation

- Requires minimum room size of 8' x 8' x 8' (2438 x 2438 x 2438 mm)

Installation Notes

Install this product according to the installation instructions.

For use with showerheads or handsprays rated at 0.9 gal/min (3.4 l/min) or higher.

