



Toccata® | K-3349-1

15" top-mount single-bowl bar sink

Features

- 18" (457 mm) minimum base cabinet width
- Single bowl
- 7" depth
- Single faucet hole
- Includes installation hardware



Codes/Standards

ADA compliant when installed to the specific requirements of these regulations.

ADA permits a parallel approach to wet bars.



ASME A112.19.3/CSA B45.4

ADA

ICC/ANSI A117.1

Warranty

See website for detailed warranty information.

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

Technical Information

All product dimensions are nominal.

Number of Deck Holes:	1
Faucet Hole(s) Size:	1-7/16" (37 mm)
Drain Hole Diameter:	3-5/8" (92 mm)
Minimum Base Cabinet Width:	18" (457 mm)
Basin Configuration:	Single Bowl
Basin Length:	12" (305 mm)
Basin Width:	9-1/2" (241 mm)
Basin Depth:	7" (178 mm)
Cutout:	Top-mount, 14-1/2" x 14-1/2" (368 mm x 368 mm) with 1/2" (13 mm) radius corners

Material

- Premium 19-gauge stainless steel

Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner


K-8801 Sink drain and strainer with tailpiece

K-8799 Sink drain and strainer basket, less tailpiece



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-29-2026 19:05 - US-CA



Installation

- Top-mount

Installation Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.

ADA permits a parallel approach to wet bars.

